

Patriot HS and Midi Flag Hinge - Profile Matrix

Please note this is a guide only. We cannot guarantee the data below. Profiles and gaskets may change without our knowledge or vary from either CAD data supplied or manufactures recommendations . It is strongly recommended that all configurations are trailed prior to ordering product

Patriot HS Hinge

Product Code	Step Height	Shim Height Options	Sim Part No.
TRO-0740-2007	16mm	1.25mm	0740-039
TRO-0740-2005	19.25mm	2.5mm	0740-022
TRO-0740-2006	21.5mm	7.5mm	0740-025

Midi Hinge

Product Code	Step Height	Shim Height Options	Sim Part No.
TRO-0780-2005	16mm	1.25mm	0780-027
TRO-0780-2002	19.25mm	2.5mm	0780-016
TRO-0780-2004	21.5mm	7.5mm	0780-024

Profile	Step Height	Hinge type	Packers	Nominal Adjustment
Deceuninck 2500	20.0	19.25mm	None	0.75mm out
Deceuninck 3000	20.0	19.25mm	None	0.75mm out
Deceuninck LCA 70	22.0	21.5mm	None	0.50mm out
Diplomat	22.0	21.5mm	None	0.50mm out
Duraflex Diamond	15.5	16mm	None	0.50mm in
Elite 63 (Spectus/HW)	18.0	16mm	1x2.5	0.50mm in
	or	19.25mm	None	1.25mm in
Elite 70 (Spectus/HW)	21.5	21.5mm	None	None
Eurocell Logik Ovalo	21.0	21.5mm	None	0.50mm in
Eurocell Logik 70	21.0	21.5mm	None	0.50mm in
Eurocell 70mm - 13.5mm	17.0	16mm	1x1.25	0.25mm in
Eurocell NBC 60	15.0	16mm	None	1.00 mm in
K2 Renaissance	20.0	19.25mm	None	0.75mm out
KBE 70mm	20.5	19.25mm	None	1.25mm out
Kommerling Gold 58mm	15.5	16mm	None	0.50mm in
Kommerling Gold 70 mm	18.0	16mm	1x2.5	0.50mm in
	or	19.25mm	None	1.25mm in
Kommerling Connoisseur	21.5	21.5mm	None	None
KS Fortuna	19.0	19.25mm	None	0.25mm in
LB 6000	15.5	16mm	None	0.5mm in
LB 7000	17.5	16mm	1x1.25	0.25mm out
LB 8000	17.5	16mm	1x1.25	0.25mm out
Liniar	21.0	21.5mm	None	0.50mm in
Plastmo Index 60mm	16.4	16mm	None	0.50mm out
Plastmo Index 70mm	24.0	21.5mm	1x2.5	None
Profile 22	18.0	16mm	1x2.5	0.50mm in
	or	19.25mm	None	1.25mm in
Profile 22 FS	28.0	21.5mm	1x7.5	1.00mm in
Rehau Edge IG 70mm Sculptured	21.0	21.5mm	None	0.50mm in
Rehau Edge 70mm Non IG	20.0	19.25mm	None	0.75mm out

Rehau S706	19.0	19.25mm	None	0.25mm in
Rahue 706 IG	21.3	21.5mm	None	None
Selecta 8000	?			
Selecta Advanced 70	18.0	16mm	1x2.5	0.50mm in
"	or	19.25mm	None	1.25mm in
Spectus Sightline 70	20.0	19.25mm	None	0.75mm out
Synseal (PFL) Legend 70	18.5	16mm	1x2.5	None
	or	19.25mm	None	0.75mm in
Synseal Shield	17	16mm	1x1.25	0.25mm in
Synseal Synerjy	21.0	21.5mm	None	0.50mm in
Swish 24/7	18.0	16mm	1x2.5	0.50mm in
	or	19.25mm	None	1.25mm in
Veka Matrix 58	16.0	16mm	None	None
Veka Matrix 70	16.5	16mm	None	0.50mm out
Veka Matrix 70 Sculptured	?			
WHS Halo Classique	15.0	16mm	None	1.00 mm in
WHS Halo Eclipse	19.0	19.25mm	None	0.25mm in
WHS Rustique OLD	15.0	16mm	None	1.00 mm in
WHS System 10 OLD	15.0	16mm	None	1.00 mm in
WHS System 10 MK2	23.0	21.5mm	1x2.5	1.00 mm in

Last Revised 03-03-2010

End